

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348855511](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: .635mm, 1.50mm, Power CMX Connector, 55 Circuits, Right Wire Output, Black Coding

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Application Specification AS-34885-002-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Housings
Series [34885](#)
Application Automotive, Power, Wire-to-Board
Comments Current tested on 0.85mm² wire for CTX64 and CTX150

2A for CTX64,10A for CTX150
Sealed, hybrid, high-density, a new generation of CMC, suitable for rugged, powertrain applications in transportation market
More Detailed Tech Information [CMC and CMX Sealed, Hybrid, Modular Connectors](#)
Overview [CMX](#)
Product Name [889056357517](#)
UPC

Physical

Circuits (maximum) 55
Circuits Detail 35x0.64mm, 20x1.50mm terminals
Color - Resin Black
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 40.342/g
Number of Rows 5
Packaging Type Carton
Panel Mount No
Pitch - Mating Interface 2.50mm, 3.70mm
Stackable No
Temperature Range - Operating -40° to +120°C

Electrical

Current - Maximum per Contact 10.0A, 2.0A

Material Info

Reference - Drawing Numbers

Application Specification [AS-34885-002-001](#)
Sales Drawing [SD-34885-001-001](#)



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34885](#) Series

Mates With

CMX Header [5600451201](#)

Use With

CTX64 Female Terminal [34803](#) , CTX150 Female Terminal [34805](#) , CTX150 Plugs [643251010](#) , [643251023](#) , CMX Wire Cap [5027300001](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34885-5511](#)