

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348994076](#)
Status: **Active**
Overview: MXP120 Sealed Connector System
Description: MXP120 Sealed Male Blade Connector with 7.00mm Clip-Slot, 4 Circuit, Yellow SIR Housing (T3-V2-S2 - 125°C on-engine vibration), Wire Dress Cover Interface Option 2, Key G

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34900-0001-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-31301-898-001 (PDF)	

Application tooling part link

Application Tooling Part Link	63824-6300
-------------------------------	------------

General

Product Family	Crimp Housings
Series	34899
Application	Automotive, Safety, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	MXP120 Sealed Connector System
Polarization	G
Product Name	MXP120 Sealed
UPC	889056519304

Physical

Circuits (maximum)	4
Color - Resin	Yellow
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	5.300/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	AS-34900-0001-001
Packaging Specification	PK-31301-898-001
Sales Drawing	SD-34899-2001-001, SD-34899-6001-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[34899](#) Series

Mates With

MXP120 Female Receptacle [34900](#)

Use With

Tyco 1.2 MCON terminals
Or
Kostal MLK 1.2 terminals

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Extraction Toolkit for MXP120 Sealed Connection System	638246300
--	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34899-4076