


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0349580380**
Status: **Active**
Overview: Mini50 Connection Systems
Description: Mini50 Unsealed Vertical Header, 3 Rows, 38 Circuit, Polarization Option A, Black, Tray

Documents:

3D Model	Packaging Specification PK-31302-070-001 (PDF)
Drawing (PDF)	Test Summary TS-34961-001 (PDF)
Product Specification PS-34959-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34959-001-001 (PDF)	Product Literature (PDF)



Series image - Reference only

General

Product Family	PCB Headers
Series	34958
Application	Power, Signal, Wire-to-Board
Overview	<u>Mini50 Connection Systems</u>
Product Literature Order No	987650-5442
Product Name	Mini50
UPC	887191714608

Physical

Breakaway	No
Circuits (Loaded)	38
Circuits (maximum)	38
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	SPS
Number of Rows	3
Orientation	Vertical
PC Tail Length	3.07mm
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-34959-001-001
---------------------------	------------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[34958](#) Series

Mates With

[34959](#) Mini50 Unsealed 3 Row Receptacle

Packaging Specification
Product Specification
Sales Drawing
Test Summary

PK-31302-070-001
PS-34959-001-001
SD-34958-300-001
TS-34961-001

This document was generated on 07/27/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34958-0380](#)