

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349590349](#)
Status: **Active**
Overview:
Description: Mini50 Unsealed Receptacle, 3 Rows, without CPA, 34 Circuits, Polarization Option C, Dark Gray

Documents:

3D Model (PDF)	Application Specification AS-34959-001-001 (PDF)
3D Model	Packaging Specification PK-31301-538-001 (PDF)
Drawing (PDF)	Test Summary TS-34961-001-001 (PDF)
Product Specification PS-34959-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 349590001-AS-CH-000 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	34959
Application	Automotive, Power, Wire-to-Board
Overview	mini50_unsealed_connection_systems
Polarization	C
Product Name	Mini50
UPC	887191704494


Physical

Circuits (maximum)	34
Color - Resin	Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.267/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	349590001-AS-CH-000, AS-34959-001-001
Packaging Specification	PK-31301-538-001
Product Specification	PS-34959-001-001
Sales Drawing	SD-34959-030-001
Test Summary	TS-34961-001-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

[34959 Series](#)

Mates With

Mini50 Vertical Headers:
 [349580342](#) , [349587342](#) , [349588342](#)
 Mini50 Right-Angle Headers:
 [349610342](#) , [349617342](#) , [349618342](#)

Use With

CTX50 Unsealed Terminals [560023](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34959-0349](#)