

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349674001

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option A, Black



Series image - Reference only

Documents:	
3D Model	Application Specification AS-34894-0001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-898-001 (PDF)
Drawing (PDF)	Test Summary 349670001-TS-000 (PDF)
Product Specification 349670001-000 (PDF)	Datasheet (PDF)
Application Specification 348940001-AS-CH-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	34967
Application	Automotive, Power, Sealed, Wire-to-Board
Comments	-40°C to +105°C operating temperature for tin terminals -40°C to +125°C operating temperature for silver terminals
Overview	Mini50 Connection Systems
Polarization	A
Product Name	Mini50 Sealed
UPC	887191620381
Physical	
Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	2.765/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C
Material Info	
Reference - Drawing Numbers	
Application Specification	348940001-AS-CH-000, AS-34894-0001-001
Packaging Specification	PK-31301-898-001
Product Specification	349670001-000
Sales Drawing	347350050-000, 349674000-000, 349684800-000
Test Summary	349670001-TS-000

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

34967 Series

Mates With

Molex does not manufacture the mating header interface. To provide you with maximum design flexibility, we include the interface specification drawing with the part drawing, and a 3D model is available H a>, so that you may design the interface into your device as you require.

Use With

CTX50 Sealed Receptacle Terminal [34905](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34967-4001