

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349674003](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option C, Dark Gray



Series image - Reference only

Documents:	
3D Model	Application Specification AS-34894-0001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-898-001 (PDF)
Drawing (PDF)	Test Summary 349670001-TS-000 (PDF)
Product Specification 349670001-000 (PDF)	Datasheet (PDF)
Application Specification 348940001-AS-CH-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	34967
Application	Automotive, Power, Sealed, Wire-to-Board
Comments	-40°C to +105°C operating temperature for tin terminals -40°C to +125°C operating temperature for silver terminals
Overview	Mini50 Connection Systems
Polarization	C
Product Name	Mini50 Sealed
UPC	887191620404

Physical	
Circuits (maximum)	4
Color - Resin	Black, Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	3.300/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C

Material Info	
Reference - Drawing Numbers	
Application Specification	348940001-AS-CH-000, AS-34894-0001-001
Packaging Specification	PK-31301-898-001
Product Specification	349670001-000
Sales Drawing	347350050-000, 349674000-000, 349684800-000
Test Summary	349670001-TS-000

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[34967 Series](#)

Mates With
Molex does not manufacture the mating header interface. To provide you with maximum design flexibility, we include the interface specification drawing with the part drawing, and a 3D model is available H a>, so that you may design the interface into your device as you require.

Use With
CTX50 Sealed Receptacle Terminal [34905](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34967-4003