

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349671007](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Sealed Receptacle, Single Row, without CPA, 10 Circuits, Polarization Option C, Dark Gray

Documents:

3D Model	Application Specification AS-34894-0001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-898-001 (PDF)
3D Model (PDF)	Test Summary 349670001-TS-000 (PDF)
Product Specification 349670001-000 (PDF)	Datasheet (PDF)
Application Specification 348940001-AS-CH-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	34967
Application	Automotive, Power, Sealed, Wire-to-Board
Comments	-40°C to +105°C operating temperature for tin terminals -40°C to +125°C operating temperature for silver terminals
Overview	Mini50 Connection Systems
Polarization	C
Product Name	Mini50 Sealed
UPC	889056821872

Physical

Circuits (maximum)	10
Color - Resin	Black, Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	5.173/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	348940001-AS-CH-000, AS-34894-0001-001
Packaging Specification	PK-31301-898-001
Product Specification	349670001-000
Sales Drawing	347350050-000, 349671000-000, 349681800-000
Test Summary	349670001-TS-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34967 Series](#)

Mates With

Molex does not manufacture the mating header interface. To provide you with maximum design flexibility, we include the interface specification drawing with the part drawing, and a 3D model is available a>, so that you may design the interface into your device as you require.

Use With

CTX50 Sealed Receptacle Terminal [34905](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34967-1007