

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349674002

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option B, Light Gray

Documents:

- 3D Model

Application Specification AS-34894-0001-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-31301-898-001 (PDF)
- 3D Model (PDF)

Test Summary 349670001-TS-000 (PDF)
- Product Specification 349670001-000 (PDF)

Datasheet (PDF)
- Application Specification 348940001-AS-CH-000 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Crimp Housings

Series

34967

Application

Automotive, Power, Sealed, Wire-to-Board

Comments

-40°C to +105°C operating temperature for tin terminals

-40°C to +125°C operating temperature for silver terminals

Overview

Mini50 Connection Systems

Polarization

B

Product Name

Mini50 Sealed

UPC

887191620398

Physical

Circuits (maximum)

4

Color - Resin

Black, Gray (Light)

Gender

Receptacle

Glow-Wire Capable

No

Keying to Mating Part

Yes

Lock to Mating Part

Yes

Material - Resin

SPS/Nylon

Net Weight

3.300/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

1.80mm

Pitch - Termination Interface

1.80mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-40° to +105°C, -40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification

348940001-AS-CH-000, AS-34894-0001-001

Packaging Specification

PK-31301-898-001

Product Specification

349670001-000

Sales Drawing

347350050-000, 349674000-000, 349684800-000

Test Summary

349670001-TS-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

34967 Series

Mates With

Molex does not manufacture the mating header interface. To provide you with maximum design flexibility, we include the interface specification drawing with the part drawing, and a 3D model is available H a>, so that you may design the interface into your device as you require.

Use With

CTX50 Sealed Receptacle Terminal [34905](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34967-4002](#)