

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349674025

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Sealed Receptacle, Single Row, without CPA, 4 Circuits, Polarization Option A, Terminal Position 2 Plugged, Black

- Documents:
- 3D Model

Packaging Specification PK-31301-898-001 (PDF)
- 3D Model (PDF)

Test Summary 349670001-TS-000 (PDF)
- Drawing (PDF)

Datasheet (PDF)
- Product Specification 349670001-000 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification AS-34894-0001-001 (PDF)

Product Literature (PDF)

General

Product Family

Series

Application

Comments

Crimp Housings

34967

Automotive, Power, Sealed, Wire-to-Board

-40°C to +105°C operating temperature for tin terminals

-40°C to +125°C operating temperature for silver terminals

Mini50 Connection Systems

A

Mini50 Sealed

889056821841

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

4

Black

Receptacle

No

Yes

Yes

SPS/Nylon

3.309/g

1

Bag

No

1.80mm

1.80mm

Yes

No

-40° to +105°C, -40° to +125°C

Material Info

Engineering Number

CVP34967-4025

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

Test Summary

AS-34894-0001-001

PK-31301-898-001

349670001-000

347350050-000, 349674000-000, 349684800-000

349670001-TS-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34967 Series

Mates With

Molex does not manufacture the mating header interface. To provide you with maximum design flexibility, we include the interface specification drawing with the part drawing, and a 3D model is available H a>, so that you may design the interface into your device as you require.

Use With

CTX50 Sealed Receptacle Terminal [34905](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34967-4025](#)