

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0350211160

Status:

Active

Overview:

Board-in Connectors

Description:

2.50mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Tin (Sn) Plating, 22-28 AWG, Reel



Series image - Reference only

Documents:	
3D Model	Product Specification PS-35021-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-35021-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	35021
Application	Signal, Wire-to-Board
Comments	Right Angle, Use with Housing 35023
Crimp Quality Equipment	Yes
Overview	Board-in Connectors
Product Name	Board-in
UPC	822348251179
Physical	
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.033/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	125V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Crimp Specification	CS-35021-001-001
Packaging Specification	PK-35021-001-001
Product Specification	PS-35021-001-001
Sales Drawing	SD-35021-002-001

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

35021 Series

Use With

Board-In Crimp Housing 35022 , 212415

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Right-Angle Board-in Crimp Terminals	638116900
FineAdjust Applicator for Board-in Right-Angle 2.50mm Terminal for 22-28 AWG	639041800
T2 Terminator for Right-Angle, 2.50mm	639129100

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[35021-1160 \(Mouser Reel\)](#) [35021-1160 \(Cut Strip\)](#) [35021-1160 \(Loose Piece\)](#)