

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0350539002](#)
Status: **Active**
Description: 2.50mm Pitch Wire-to-Wire Terminal, Male, 22-28 AWG (0.33-0.81mm²), Tin-plated, Reel, for 35184 Housing

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-35053-001-001 \(PDF\)](#)
[Product Specification PS-35184-001-001 \(PDF\)](#)
[Product Specification PS-35531-001-001 \(PDF\)](#)
[Packaging Specification PK-35053-9002-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Crimp Terminals
Series [35053](#)
Application Signal
Crimp Quality Equipment Yes
Product Name N/A
UPC 800754253345

Physical
Gender Male
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.073/g
Packaging Type Reel
Plating min - Mating 0.813µm
Plating min - Termination 0.813µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.15-1.90mm
Wire Size AWG 22, 24, 26, 28
Wire Size mm² N/A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
[Packaging Specification PK-35053-9002-001](#)
[Product Specification PS-35053-001-001, PS-35184-001-001, PS-35531-001-001](#)
[Sales Drawing SD-35053-9002-001](#)



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[35053](#) Series

Mates With
[5103](#) Crimp Terminal

Use With
[35184](#)

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	638132700
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 22-28 AWG	638190800

FineAdjust Applicator639007900
for 2.50mm Wire-
to-Wire Male Crimp
Terminal, 22-28
AWG Wire
T2 Terminator 639107900
Tooling Die for Wire-
to-Wire Male Crimp
Terminal, 22-28
AWG

This document was generated on 09/13/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[35053-9002](#) [35053-9002 \(Cut Strip\)](#) [35053-9002 \(Mouser Reel\)](#) [35053-9002 \(Loose Piece\)](#)