

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0354539802

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

6.35mm Tab Heavy, Tab Terminal, Type B, 16-18 AWG (1.31-0.80mm²), Pre-Tin Plated

Documents:

- [Drawing \(PDF\)](#)
- [Product Specification PS-35546-002 \(PDF\)](#)
- [Packaging Specification PK-35452-002-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Quick Disconnects
Series	35453
Crimp Quality Equipment	Yes
Insulated	No
Overview	Standard Quick-Disconnect Terminals
Product Name	N/A
Type	Quick Disconnect
UPC	800753255883

Physical

Barrel Type	Open
Gender	Male
Glow-Wire Capable	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Net Weight	0.912/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-40° to +120°C
Wire Size AWG	16, 18


Electrical

Voltage - Maximum	250V
-------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35452-002-001
Product Specification	PS-35546-002
Sales Drawing	SD-35452-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

35453 Series

Use With

35546 , 35547

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for 6.35mm Heavy Tab Terminals, 12-14 AWG	638133100
Hand Crimp Tool for 6.35mm Heavy Tab Terminals	638192700
FineAdjust for 6.35mm Tab Heavy Tab Crimp	639009000

Terminals, 16-18
AWG Wire
T2 Terminator for 639109000
6.35mm Tab Heavy
Tab Crimp Terminal

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

35453-9802