

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0359659220

Status:


Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type C, Natural, Glow-Wire Capable



Series image - Reference only

Documents:	
3D Model	Application Specification 351500000ASKOR-000 (PDF)
3D Model (PDF)	Packaging Specification PK-35965-001-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification 351800400-001 (PDF)	Brochure (PDF)
Product Specification 351800600-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 351500000ASENG-000 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	35965
Application	Power, Wire-to-Wire
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	822350213455
Physical	
Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	2.941/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C
Material Info	
Reference - Drawing Numbers	
Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	PK-35965-001-001
Product Specification	351800400-001, 351800600-001
Sales Drawing	359659220-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

35965 Series

Mates With

VersaBlade Multi-Module 2-2-2 Receptacle Housing [351800600](#) , [351800609](#) , [351803609](#) , [351804609](#)

Use With

VersaBlade Crimp Terminals [35748](#)

VersaBlade TPA [359650290](#) , [359650292](#) , [359650293](#) , [1040810282](#) , [495470392](#) (Upper), [495480390](#) (Lower)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35965-9220](#)