

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0387104703

Status:


Active

Overview:

Beau Barrier Strips

Description:

9.53mm Pitch Beau PCB Terminal Strip, Low Profile, Insulated PC Tail, 3 Circuits



|                |                                              |
|----------------|----------------------------------------------|
| Documents:     |                                              |
| 3D Model       | Product Specification PS-38710-001-001 (PDF) |
| Drawing (PDF)  | RoHS Certificate of Compliance (PDF)         |
| 3D Model (PDF) |                                              |

|                                |                                    |
|--------------------------------|------------------------------------|
| General                        |                                    |
| Product Family                 | Terminal Blocks                    |
| Series                         | 38710                              |
| Application                    | N/A                                |
| Component Type                 | One Piece                          |
| Overview                       | Beau Barrier Strips                |
| Product Name                   | Fixed Mount Barrier                |
| Type                           | Barrier Strip                      |
| UPC                            | 800756283104                       |
| Physical                       |                                    |
| Circuits (Loaded)              | 3                                  |
| Circuits (maximum)             | 3                                  |
| Color - Resin                  | Black                              |
| Entry Angle                    | Horizontal                         |
| Lock to Mating Part            | None                               |
| Material - Metal               | Brass                              |
| Material - Plating Mating      | Tin                                |
| Material - Plating Termination | Tin                                |
| Material - Resin               | Polyester                          |
| Net Weight                     | 29.000/g                           |
| Number of Rows                 | 1                                  |
| Orientation                    | Horizontal                         |
| PC Tail Length                 | 5.30mm                             |
| PCB Retention                  | Yes                                |
| Panel Mount                    | No                                 |
| Pitch - Mating Interface       | 9.53mm                             |
| Pitch - Termination Interface  | 9.53mm                             |
| Polarized to Mating Part       | No                                 |
| Shrouded                       | Dual-Barrier                       |
| Stackable                      | No                                 |
| Surface Mount Compatible (SMC) | No                                 |
| Temperature Range - Operating  | -40° to +130°C                     |
| Termination Interface: Style   | Screw or Lug                       |
| Wire Size AWG                  | 14, 16, 18, 20, 22                 |
| Wire Size mm²                  | 0.50-1.50                          |
| Electrical                     |                                    |
| Current - Maximum per Contact  | 15.0A                              |
| Voltage - Maximum              | 300V                               |
| Material Info                  |                                    |
| Engineering Number             | 71303                              |
| Reference - Drawing Numbers    |                                    |
| Product Specification          | PS-38710-001-001                   |
| Sales Drawing                  | SD-38710-006-001, SD-38710-006-002 |

|                                                                      |                          |
|----------------------------------------------------------------------|--------------------------|
| EU ELV<br>Compliant                                                  |                          |
| EU RoHS<br>Compliant                                                 | China RoHS               |
| REACH SVHC<br>Not Contained Per -<br>D(2021)4569-DC (8<br>July 2021) |                          |
| Halogen-Free<br>Status<br>Not Relevant                               |                          |
| For more information, please visit <a href="#">Contact US</a>        |                          |
| China ROHS<br>ELV                                                    | Green Image<br>Compliant |
| RoHS Phthalates                                                      | Not Contained            |

Search Parts in this Series  
38710 Series

Mates With  
N/A

This document was generated on 01/11/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38710-4703](#)