

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0387206218](#)
Status: **Active**
Overview: [Beau Barrier Strips](#)
Description: 9.53mm Pitch Beau PCB Terminal Strip, with Mounting Ends, 18 Circuits

Documents:
[3D Model](#) [Product Specification PS-38710-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)


General
Product Family Terminal Blocks
Series [38720](#)
Application N/A
Component Type One Piece
Overview [Beau Barrier Strips](#)
Product Name Fixed Mount Barrier
Type Barrier Strip
UPC 800756333540

Physical
Circuits (Loaded) 18
Circuits (maximum) 18
Color - Resin Black
Entry Angle Horizontal
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyester
Net Weight 9.870/g
Number of Rows 1
Orientation Horizontal
PC Tail Length 4.80mm
PCB Retention Yes
PCB Thickness - Recommended 3.18mm
Panel Mount No
Pitch - Mating Interface 9.53mm
Pitch - Termination Interface 9.53mm
Plating min - Mating 3.810µm
Plating min - Termination 3.810µm
Polarized to Mating Part No
Shrouded Dual-Barrier
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40° to +130°C
Wire Size AWG 14, 16, 18, 20, 22
Wire Size mm² 0.50-1.50

Electrical
Current - Maximum per Contact 15.0A
Voltage - Maximum 300V

Solder Process Data
Lead-freeProcess Capability WAVE

Material Info
Engineering Number 72518



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[38720 Series](#)

Reference - Drawing Numbers

Product Specification	PS-38710-001-001
Sales Drawing	SD-38720-001-001

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38720-6218](#)