

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395005005

Status:

Active

Overview:

Description:

3.50mm Pitch Eurostyle Horizontal Plug, Green Housing, 5 Circuits

|                               |                           |
|-------------------------------|---------------------------|
| Agency Certification          |                           |
| UL                            | E48521                    |
| General                       |                           |
| Product Family                | Terminal Blocks           |
| Series                        | 39500                     |
| Application                   | N/A                       |
| Component Type                | Plug                      |
| Overview                      | eurostyle_terminal_blocks |
| Product Name                  | ESE, Eurostyle Pluggable  |
| Type                          | Euro Block                |
| UPC                           | 822350427265              |
| Physical                      |                           |
| Circuits (Loaded)             | 5                         |
| Entry Angle                   | Vertical                  |
| Lock to Mating Part           | None                      |
| Net Weight                    | 24.000/g                  |
| Number of Rows                | 1                         |
| Orientation                   | Horizontal                |
| Panel Mount                   | No                        |
| Pitch - Mating Interface      | 3.50mm                    |
| Pitch - Termination Interface | 3.50mm                    |
| Polarized to Mating Part      | Yes                       |
| Stackable                     | No                        |
| Temperature Range - Operating | -40° to +105°C            |
| Wire Size AWG                 | 16, 18, 20, 22, 24, 30    |
| Wire Size mm²                 | 0.05-1.50                 |
| Electrical                    |                           |
| Current - Maximum per Contact | 8.0A                      |
| Voltage - Maximum             | 300V                      |
| Material Info                 |                           |
| Engineering Number            | 395005006                 |
| Reference - Drawing Numbers   |                           |
| Product Specification         | PS-39500-001-001          |
| Sales Drawing                 | SD-39500-001-001          |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Relevant |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

39500 Series

Mates With

39501 Vertical PCB Header, 39502 Horizontal PCB Header, Most 3.50mm Pitch Industry Standard PCB Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39500-5005