

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0393730008

Status:

Active

Overview:


Eurostyle Terminal Blocks

Description:

7.50mm Beau Eurostyle Horizontal PCB Header, Closed Ends, 8 Circuits

|                                |                                                      |
|--------------------------------|------------------------------------------------------|
| Documents:                     |                                                      |
| <a href="#">3D Model</a>       | <a href="#">Drawing (PDF)</a>                        |
| <a href="#">3D Model (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

|                                |                           |
|--------------------------------|---------------------------|
| Agency Certification           |                           |
| UL                             | E48521                    |
| General                        |                           |
| Product Family                 | Terminal Blocks           |
| Series                         | 39373                     |
| Application                    | N/A                       |
| Component Type                 | PCB Header                |
| Overview                       | Eurostyle Terminal Blocks |
| Product Name                   | Eurostyle Pluggable       |
| Type                           | Euro Block                |
| UPC                            | 822348042111              |
| Physical                       |                           |
| Circuits (Loaded)              | 8                         |
| Circuits (maximum)             | 8                         |
| Entry Angle                    | 90° Angle                 |
| Flammability                   | 94V-0                     |
| Lock to Mating Part            | None                      |
| Net Weight                     | 25.000/g                  |
| Number of Rows                 | 1                         |
| Orientation                    | Right Angle               |
| PC Tail Length                 | 3.50mm                    |
| PCB Retention                  | None                      |
| Panel Mount                    | No                        |
| Pitch - Mating Interface       | 7.50mm                    |
| Pitch - Termination Interface  | 7.50mm                    |
| Polarized to Mating Part       | Yes                       |
| Shrouded                       | Closed Ends               |
| Stackable                      | No                        |
| Surface Mount Compatible (SMC) | No                        |
| Temperature Range - Operating  | 110°C                     |
| Wire Size AWG                  | N/A                       |
| Electrical                     |                           |
| Current - Maximum per Contact  | 15.0A                     |
| Voltage - Maximum              | 300V                      |
| Material Info                  |                           |
| Engineering Number             | MX-CIM089P3-0N            |
| Reference - Drawing Numbers    |                           |
| Sales Drawing                  | SD-39373-001-001          |



|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Relevant |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

39373 Series

Mates With

39371 , 39374 Plugs

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39373-0008](#)