

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395133807

Status:


Active

Overview:

Eurostyle Terminal Blocks

Description:

3.81mm Pitch Eurostyle Vertical Plug, with Standard Imprinting, Front Wire Entry, Gold (Au) Plated, 7 Circuits



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Specification PS-39500-001-001 \(PDF\)](#)

|                               |                                           |
|-------------------------------|-------------------------------------------|
| Agency Certification          |                                           |
| UL                            | E48521                                    |
| General                       |                                           |
| Product Family                | Terminal Blocks                           |
| Series                        | 39513                                     |
| Application                   | N/A                                       |
| Comments                      | with Standard Imprinting Front Wire Entry |
| Component Type                | Plug                                      |
| Overview                      | Eurostyle Terminal Blocks                 |
| Product Name                  | ESE, Eurostyle Pluggable                  |
| Type                          | Euro Block                                |
| UPC                           | 822350424943                              |
| Physical                      |                                           |
| Circuits (Loaded)             | 7                                         |
| Entry Angle                   | Horizontal                                |
| Lock to Mating Part           | None                                      |
| Number of Rows                | 1                                         |
| Orientation                   | Vertical                                  |
| Panel Mount                   | No                                        |
| Pitch - Mating Interface      | 3.81mm                                    |
| Pitch - Termination Interface | 3.81mm                                    |
| Polarized to Mating Part      | Yes                                       |
| Stackable                     | No                                        |
| Temperature Range - Operating | -40° to +105°C                            |
| Wire Size AWG                 | 16, 18, 20, 22, 24, 26, 28, 30            |
| Wire Size mm²                 | 0.05-1.31                                 |
| Electrical                    |                                           |
| Current - Maximum per Contact | 8.0A                                      |
| Voltage - Maximum             | 300V                                      |
| Material Info                 |                                           |
| Reference - Drawing Numbers   |                                           |
| Product Specification         | PS-39500-001-001                          |
| Sales Drawing                 | SD-39513-001                              |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Relevant |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

39513 Series

Mates With

Most 3.81mm Pitch Industry Standard PCB Headers, [39511](#) Vertical PCB Header, [39512](#) Horizontal PCB Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39513-3807](#)