

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395211005

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.00mm Pitch Eurostyle Vertical PCB Header, 5 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-39500-001-001 (PDF)


RoHS Certificate of Compliance (PDF)

|                               |                           |
|-------------------------------|---------------------------|
| Agency Certification          |                           |
| UL                            | E48521                    |
| General                       |                           |
| Product Family                | Terminal Blocks           |
| Series                        | 39521                     |
| Application                   | N/A                       |
| Component Type                | PCB Header                |
| Overview                      | Eurostyle Terminal Blocks |
| Product Name                  | ESE, Eurostyle Pluggable  |
| Type                          | Euro Block                |
| UPC                           | 822350476355              |
| Physical                      |                           |
| Circuits (Loaded)             | 5                         |
| Entry Angle                   | N/A                       |
| Lock to Mating Part           | Yes                       |
| Net Weight                    | 2.000/g                   |
| Number of Rows                | 1                         |
| Orientation                   | Vertical                  |
| PC Tail Length                | 3.90mm                    |
| PCB Thickness - Recommended   | 3.20mm                    |
| Panel Mount                   | No                        |
| Pitch - Mating Interface      | 5.00mm                    |
| Pitch - Termination Interface | 5.00mm                    |
| Polarized to Mating Part      | Yes                       |
| Shrouded                      | Closed Ends               |
| Stackable                     | No                        |
| Temperature Range - Operating | -40° to +105°C            |
| Wire Size AWG                 | N/A                       |
| Electrical                    |                           |
| Current - Maximum per Contact | 15.0A                     |
| Voltage - Maximum             | 300V                      |

Material Info

Reference - Drawing Numbers

|                       |                  |
|-----------------------|------------------|
| Product Specification | PS-39500-001-001 |
| Sales Drawing         | SD-39521-002-001 |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2021)4569-DC (8 July 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

39521 Series

Mates With

39520 Horizontal Plug, 39523 Vertical Plug, Most 5.00mm Pitch Industry Standard Plugs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39521-1005](#)