

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0398900308

Status:


Active

Overview:

Eurostyle Terminal Blocks

Description:

5.00mm Pitch Beau Eurostyle Low Profile, Single Level Modular Terminal Block, 8 Circuits



|                                |                                                      |
|--------------------------------|------------------------------------------------------|
| Documents:                     |                                                      |
| <a href="#">3D Model</a>       | <a href="#">Drawing (PDF)</a>                        |
| <a href="#">3D Model (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

|                                |                                |
|--------------------------------|--------------------------------|
| Agency Certification           |                                |
| UL                             | E48521                         |
| General                        |                                |
| Product Family                 | Terminal Blocks                |
| Series                         | 39890                          |
| Application                    | N/A                            |
| Component Type                 | One Piece                      |
| Overview                       | Eurostyle Terminal Blocks      |
| Product Name                   | Eurostyle Fixed Mount          |
| Type                           | Euro Block                     |
| UPC                            | 756054528228                   |
| Physical                       |                                |
| Circuits (Loaded)              | 8                              |
| Circuits (maximum)             | 8                              |
| Entry Angle                    | Horizontal                     |
| Flammability                   | 94V-0                          |
| Lock to Mating Part            | None                           |
| Net Weight                     | 7.120/g                        |
| Number of Rows                 | 1                              |
| Orientation                    | Vertical                       |
| PC Tail Length                 | 3.51mm                         |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 2.40mm                         |
| Panel Mount                    | No                             |
| Pitch - Mating Interface       | 5.00mm                         |
| Pitch - Termination Interface  | 5.00mm                         |
| Polarized to Mating Part       | No                             |
| Shrouded                       | Fully                          |
| Stackable                      | Yes                            |
| Surface Mount Compatible (SMC) | No                             |
| Temperature Range - Operating  | 105°C                          |
| Wire Size AWG                  | 16, 18, 20, 22, 24, 26, 28, 30 |
| Wire Size mm²                  | 0.20-1.50                      |
| Electrical                     |                                |
| Current - Maximum per Contact  | 13.5A                          |
| Voltage - Maximum              | 300V                           |
| Material Info                  |                                |
| Engineering Number             | MX-MSB08001-0N                 |
| Reference - Drawing Numbers    |                                |
| Sales Drawing                  | SD-39890-003-001               |

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series  
39890 Series

This document was generated on 08/27/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39890-0308](#)