

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0399700312

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

10.16mm Beau Eurostyle Fixed Mount PCB Terminal Block, High Power 40A, 12 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39970

N/A

One Piece

Eurostyle Terminal Blocks

Eurostyle Fixed Mount

Euro Block

822348686735

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Entry Angle

Flammability

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Number of Rows

Orientation

PC Tail Length

PCB Retention

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Wire Size mm²

12

12

Black

Horizontal

94V-0

None

Brass, Copper

Tin

Tin

1

Vertical

4.06mm

None

No

10.16mm

10.16mm

3.810µm

3.810µm

N/A

Fully

No

No

130°C

Through Hole

10, 12, 14, 16, 18, 8

0.75-6.00

Electrical

Current - Maximum per Contact

Voltage - Maximum


40.0A

300V

Material Info

Engineering Number

973512



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/71/2019 (16 July 2019)

lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

39970 Series

This document was generated on 07/28/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39970-0312](#)