

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0428170141](#)
Status: **Active**
Overview: Mini-Fit Sr. Power Connectors
Description: Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Tin (Sn)
Replacement Part Number : <http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=0428170142428170142> (Gold)

Documents:

Drawing (PDF)	Packaging Specification PK-42815-001-001 (PDF)
Product Specification PS-42815-001-001 (PDF)	Packaging Specification PK-42815-001-002 (PDF)
Application Specification AS-42815-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	42817
Application	Power, Wire-to-Wire
Comments	High Current/Low Force Grounding Pin See Product Specification for maximum current rating by circuit size and application.
Crimp Quality Equipment	Yes
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.
Replacement Part Number	428170142 (Gold)
Replacement Part Number	428171144 (Silver)
UPC	756054457122

Physical

Gender	Male
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.370/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.57mm max.
Wire Size AWG	14, 16
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	50.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	AS-42815-001-001
Application Tooling Documents	ATS-638912000-001
Packaging Specification	PK-42815-001-001, PK-42815-001-002
Product Specification	PS-42815-001-001
Sales Drawing	SD-42817-020-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42817](#) Series

Use With

Mini-Fit Sr. Plug Housings [42818](#) , [43938](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for 10.00mm Mini-Fit Sr. Male and Female Terminals, 14-16 AWG	638113800
Extraction Tool for Mini-Fit Sr. Terminals, 8-16 AWG	638130400

Mini-Mac Applicator 638912000
for Mini-Fit Sr.
Male and Female
Terminals for 14-16
AWG Wire with
Insulation Diameter
no greater than
3.33mm

This document was generated on 09/14/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[42817-0141 \(Mouser Reel\)](#) [42817-0141 \(Cut Strip\)](#) [42817-0141 \(Loose Piece\)](#)