

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0399400406

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.08mm Pitch Beau EuroMate Pluggable PCB Terminal Block, Dual Level, 90° Wire Entry, with Retention Screws, 6 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-39940-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39940

N/A

Gold plating available

Plug

Eurostyle Terminal Blocks

EuroMate Pluggable

Euro Block

800756372846

Physical

Circuits (Loaded)

Color - Resin

Entry Angle

Flammability

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Retention

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Wire Size mm²

6

Black

Horizontal

94V-0

Yes

Nylon

120.000/g

2

Vertical

N/A

No

5.08mm

5.08mm

Yes

Tri-Barrier

No

130°C

Screw or Lug

12, 14, 16, 18, 20, 22

0.50-2.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

15.0A

300V

Material Info

Engineering Number

946806


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-39940-001-001

SD-39940-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2018 (15

January 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39940 Series

Mates With

395350006 , 395354006 , 395360006 , 395364006

This document was generated on 08/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39940-0406](#)