

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0428180412](#)
Status: **Active**
Overview: Mini-Fit Sr. Power Connectors
Description: 10.00mm Pitch Mini-Fit Sr. Plug Housing, Single Row, Panel Mount, 4 Circuit, Black

Documents:
[Drawing \(PDF\)](#) [Product Specification TS-42815-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-42818-002-001 \(PDF\)](#)
[3D Model](#) [Test Summary TS-42815-004-001 \(PDF\)](#)
[Product Specification PS-42815-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [42818](#)
Application Power, Wire-to-Board
Overview [Mini-Fit Sr. Power Connectors](#)
Product Name Mini-Fit Sr.
UPC 800754382106


Physical
Circuits (maximum) 4
Color - Resin Black
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 9.089/g
Number of Rows 1
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 10.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Electrical
Current - Maximum per Contact 50.0A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Packaging Specification PK-42818-002-001
Product Specification PS-42815-001-001, TS-42815-001-001
Sales Drawing SD-42818-XXX2-001
Test Summary TS-42815-004-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[42818](#) Series

Mates With
Mini-Fit Sr. Receptacle Housing [428160412](#)
. Mini-Fit Sr. Cable Assembly [369240401](#) ,
[369240403](#) , [369240410](#)

Use With
Terminal Position Assurance (TPA) Clip
Included. [42817](#) Male Crimp Terminals

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[42818-0412](#)