

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0399700110

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

10.16mm Beau Eurostyle Fixed Mount PCB Terminal Block, High Power 60A, 10 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39970

N/A

One Piece

Eurostyle Terminal Blocks

Eurostyle Fixed Mount

Euro Block

800756173146

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Entry Angle

Flammability

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length

PCB Retention

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Wire Size mm²

10

10

Black

Horizontal

94V-0

None

Copper

Tin

Tin

Polyester

1

Vertical

4.06mm

None

No

10.16mm

10.16mm

3.810µm

3.810µm

N/A

Fully

No

No

130°C

Through Hole

10, 12, 14, 16, 18, 6, 8

0.75-10.00

Electrical

Current - Maximum per Contact

Voltage - Maximum


60.0A

300V

Solder Process Data

Lead-freeProcess Capability

WAVE



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

39970 Series

Material Info

Engineering Number 970510

Reference - Drawing Numbers

Sales Drawing SD-39970-003

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[39970-0110](#)