

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0441330400

Status:


Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit BMI Receptacle Housing, Dual Row, Panel Mount, 4 Circuits, Polyester, UL 94V-0



Documents:	
Drawing (PDF)	Test Summary TS-43045-001-001 (PDF)
3D Model (PDF)	Test Summary TS-43045-002-001 (PDF)
3D Model	Test Summary TS-46235-001-001 (PDF)
Product Specification PS-44300-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 443000001-AS-000 (PDF)	Product Literature (PDF)
Packaging Specification PK-44133-002-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	44133
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Micro-Fit Connector System
Product Name	Micro-Fit BMI
UPC	800753132917
Physical	
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Resin	Polyester
Net Weight	1.900/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	443000001-AS-000
Packaging Specification	PK-44133-002-001
Product Specification	PS-44300-001-001
Sales Drawing	SD-44133-001-001
Test Summary	TS-43045-001-001, TS-43045-002-001, TS-46235-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

44133 Series

Mates With

443000400 Micro-Fit BMI Panel Mount Plug Housing, 44432 Micro-Fit BMI Vertical 4 Circuit Headers, 44428 Micro-Fit BMI Right Angle 4 Circuit Headers, 45280 Micro-Fit BMI CPI Vertical 4 Circuit Headers

Use With

Micro-Fit 3.0 Female Crimp Terminals 43030 , 45773
Micro-Fit RMF Female Crimp Terminals 46235
Micro-Fit 3.0 Pre-Crimped Leads 797580002 , 797580004 , 797580010 , 797580012 , 214760 , 214761

This document was generated on 08/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

44133-0400