

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0441500007

Status:

Active

Overview:

Modular Jacks and Plugs

Description:

Modular Jack, Right Angle, Low Profile, 8/8, 6 Ports

Documents:

3D Model

Packaging Specification PK-44150-004 (PDF)

Drawing (PDF)

Test Summary TS-44050-001 (PDF)

Product Specification PS-44050-003 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

44150

Comments

External Shield

Component Type

PCB Jack

Magnetic

No

Overview

Modular Jacks and Plugs

Performance Category

5, 5e

Power over Ethernet (PoE)

N/A

Product Name

RJ45

UPC

800754812818

Physical

Color - Resin

Black

Durability (mating cycles max)

500

Flammability

94V-0

Inverted / Top Latch

No

Jack Height

13.31mm

Lightpipes/LEDs

None

Material - Metal

Brass, Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

25.110/g

Orientation

Right Angle (Side Entry)

PCB Retention

Yes

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

1.02mm

Pitch - Termination Interface

1.27mm

Plating min - Mating

1.270µm

Plating min - Termination

2.540µm

Ports

6

Positions / Loaded Contacts

8/8

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40°C to +80°C

Termination Interface: Style

Through Hole

Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact


1.5A

Shielded

Yes

Voltage - Maximum

125V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

44150 Series

Mates With

FCC 68 Plugs

Solder Process Data

Lead-free	Process Capability	WAVE
-----------	--------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-44150-004
Product Specification	PS-44050-003
Sales Drawing	SD-44150-002
Test Summary	TS-44050-001

This document was generated on 07/11/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[44150-0007](#)