

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0436400309](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit 3.0 Plug Housing, Single Row, 3 Circuits, UL 94V-0, Low-Halogen Since Inception, Black

Documents:

Drawing (PDF)	Test Summary 430450005-TS-000 (PDF)
3D Model (PDF)	Test Summary TS-43045-001-001 (PDF)
3D Model	Test Summary TS-43045-002-001 (PDF)
Product Specification 436500001-PS-JA-000 (PDF)	Test Summary TS-43045-003-001 (PDF)
Product Specification 436500001-PS-KO-000 (PDF)	Test Summary TS-46235-001-001 (PDF)
Product Specification 436500001-PS-SP-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-43650-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-43640-003-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	43640
Application	Power, Wire-to-Wire
Comments	Halogen Free/Low Halogen since inception
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
UPC	883906188382

Physical

Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.293/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43640-003-001
Product Specification	436500001-PS-JA-000, 436500001-PS-KO-000, 436500001-PS-SP-000, PS-43650-001
Sales Drawing	SD-43640-001-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[43640](#) Series

Mates With

Micro-Fit 3.0 Receptacle Housing [43645](#)

Micro-Fit TPA Cable Assembly [145132](#)

Micro-Fit 3.0 Cable Assembly [214750](#) ,
[214751](#)

Use With

Micro-Fit 3.0 Crimp Terminals [43031](#)

Micro-Fit 3.0 Pre-Crimped Lead [214762](#) ,
[214763](#)

430450005-TS-000, TS-43045-001-001,
TS-43045-002-001, TS-43045-003-001,
TS-46235-001-001

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[43640-0309](#)