

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0441500029

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Right-Angle, Low Profile, 8/8, 6 Ports

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-44050-003-001 (PDF)

Packaging Specification PK-44150-004-000 (PDF)

Test Summary TS-44050-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

44150

Comments

External Shield

Component Type

PCB Jack

Magnetic

No

Overview

Magnetic and Modular Jacks/Plugs

Performance Category

5, 5e

Power over Ethernet (PoE)

N/A

Product Name

Modular Jack 8/8, RJ45

UPC

800754812849

Physical

Color - Resin

Black

Durability (mating cycles max)

500

Flammability

94V-0

Inverted / Top Latch

No

Jack Height

13.31mm

Lightpipes/LEDs

None

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

24.994/g

Orientation

Right Angle (Side Entry)

PCB Retention

Yes

PCB Thickness - Recommended

1.57mm

Packaging Type

Tray

Pitch - Mating Interface

1.02mm

Pitch - Termination Interface

1.27mm

Plating min - Mating

1.270µm

Plating min - Termination

2.540µm

Port Configuration

1x6

Positions / Loaded Contacts

8/8

Temperature Range - Operating

-40° to +85°C

Termination Interface: Style

Through Hole

Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact


1.5A

Shielded

Yes

Voltage - Maximum

150V AC (RMS)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

44150 Series

Mates With

FCC 68 Plugs

Solder Process Data

Lead-free	Process Capability	WAVE
-----------	--------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-44150-004-000
Product Specification	PS-44050-003-001
Sales Drawing	SD-44150-002-001
Test Summary	TS-44050-001-001

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

44150-0029