

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0449150022

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Plug, Category 6, Long Body, Shielded, 8/8, with Strain Relief

Documents:	
3D Model	Product Specification PS-44915-003-001 (PDF)
Drawing (PDF)	Packaging Specification PK-44915-003-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E107635
----	---------

General

Product Family	Modular Jacks/Plugs
Series	44915
Component Type	Wire Plug
Magnetic	No
Overview	Magnetic and Modular Jacks/Plugs
Performance Category	6
Power over Ethernet (PoE)	N/A
Product Name	Modular Plug 8/8, RJ45
UPC	800756395586

Physical

Color - Resin	Clear
Durability (mating cycles max)	500
Inverted / Top Latch	N/A
Jack Height	N/A
Lightpipes/LEDs	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polycarbonate
Net Weight	3.062/g
Orientation	N/A
PCB Locator	No
PCB Retention	None
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	1.27mm
Port Configuration	1x1
Positions / Loaded Contacts	8/8
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	N/A
Wire/Cable Type	Round


Electrical

Current - Maximum per Contact	1.5A
Grounding to Panel	N/A
Shielded	Yes
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-44915-003-001
-------------------------	------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

44915 Series

Mates With

FCC 68 Jacks

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Hand Crimp Tool for RJ-45 CAT5, CAT5e, CAT6, CAT6A Plugs, 22-28 AWG ServiceGrade Hand Crimp Tool - Ratchet	622020500 640160044
--	------------------------

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[44915-0022](#)