

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0457503212

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Plus Crimp Terminal, 16 AWG, Bag, Copper (Cu) Alloy, Gold (Au) Selective

Documents:

Drawing (PDF)

Product Specification PS-45750-001-001 (PDF)

Packaging Specification PK-5556-003-001 (PDF)

Test Summary 457500003-TS-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	45750
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current de-rating information. Series 45750 is Hot-Swappable
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	457503211 (Reel)
Product Name	Mini-Fit Plus
UPC	822350286107
Physical	
Durability (mating cycles max)	250
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.148/g
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.50mm
Wire Size AWG	16
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-5556-003-001
Product Specification	PS-45750-001-001
Sales Drawing	SD-45750-001-001
Test Summary	457500003-TS-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
45750 Series

Mates With
46012 Mini-Fit Plus Crimp Terminal

Use With
5557 Mini-Fit Jr., 30067 Mini-Fit TPA, 42474 Mini-Fit BMI Panel Mount, 43760 Mini-Fit BMI, 44516 Mini-Fit BMI Panel Mount Slide-N-Lock

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Extraction Tool for Mini-Fit Jr. Terminals	11030044
Hand Crimp Tool for Mini-Fit Jr. Male	2002182200

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[45750-3212](#)