

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0449150012

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Plug, Category 6, Long Body, Shielded, 8/8, without Strain Relief

Documents:

3D Model

Product Specification PS-44915-003-001 (PDF)

3D Model (PDF)

Packaging Specification PK-44915-003-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)


Agency Certification		
UL		E107635
General		
Product Family		Modular Jacks/Plugs
Series		44915
Component Type		Wire Plug
Magnetic		No
Overview		Magnetic and Modular Jacks/Plugs
Performance Category		6
Power over Ethernet (PoE)		N/A
Product Name		Modular Plug 8/8, RJ45
UPC		800756395562

Physical		
Color - Resin		Clear
Durability (mating cycles max)		500
Inverted / Top Latch		N/A
Jack Height		N/A
Lightpipes/LEDs		None
Material - Metal		Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Polycarbonate
Net Weight		2.846/g
Orientation		N/A
PCB Locator		No
PCB Retention		None
Packaging Type		Bag
Panel Mount		N/A
Pitch - Mating Interface		1.02mm
Pitch - Termination Interface		1.27mm
Port Configuration		1x1
Positions / Loaded Contacts		8/8
Temperature Range - Operating		-40° to +85°C
Termination Interface: Style		N/A
Wire/Cable Type		Round

Electrical		
Current - Maximum per Contact		1.5A
Grounding to Panel		N/A
Shielded		Yes
Voltage - Maximum		125V

Material Info

Reference - Drawing Numbers		
Packaging Specification		PK-44915-003-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

44915 Series

Mates With

FCC 68 Jacks

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for RJ-45 CAT5, CAT5e, CAT6, CAT6A Plugs, 22-28 AWG	622020500
ServiceGrade Hand Crimp Tool - Ratchet	640160044

This document was generated on 09/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[44915-0012](#)