

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0465861003

Status:

Active

Overview:

EXTreme Ten60Power High-Current Connector

Description:

EXTreme Ten60Power 7.50mm Pitch Wire-to-Board Harness Kit,3 Circuits with TPA

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

46586

Application

Power, Wire-to-Board

Comments

Includes housing and TPA

Overview

EXTreme Ten60Power High-Current Connector

Product Name

EXTreme Ten60Power

UPC

883906053383

Physical

Circuits (maximum)

3

Color - Resin

Black

Flammability

94V-0

Gender

Receptacle

Glow-Wire Capable

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Polyester

Net Weight

0.640/g

Number of Rows

1

Packaging Type

Tray

Panel Mount

No

Pitch - Mating Interface

7.50mm

Pitch - Termination Interface

7.50mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-40° to +105°C

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-46586-003-001, SD-46586-103-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Silicic acid (H2Si2O5),
barium salt (1:1),
lead-
Dicyclohexyl-
phthalate
Phenanthrene
Benzo(ghi)perylene
Dibutyltin-dichloride
1,3-Propanesultone
Terphenyl,
hydrogenated
diisohexyl phthalate
Boric acid
Tris(4-nonylphenyl,
branched and linear)
phosphi
Fluoranthene
Pyrene
Diarsenic-trioxide
Diboron-trioxide
pyrochlore, antimony
lead yellow
Lead-dinitrate
Pentalead-tetraoxide-
sulphate
Trilead-dioxide-
phosphonate
Tetralead-trioxide-
sulphate
Dioxobis(stearato)trilead
Lead titanium
zirconium oxide
Cyanamide, lead(2+)
salt (1:1)
Cadmium Hydroxide

Sulfurous Acid, Lead
Salt, Dibasic
Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[46586](#) Series

Mates With

[76546](#) EXTreme Ten60Power Vertical Plug

Use With

[44262](#) Crimp Terminal Receptacles

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[46586-1003](#)