

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0513000411](#)
Status: **Active**
Overview: CRC™ (Compact Robotic Connectors)
Description: CRC™ Shielded Rectangular I/O Receptacle Housing for Female Terminal, Power, 4 Circuits, Polarization Type A, Polarization Position A-1

Documents:

3D Model	Product Specification PS-51300-005-001 (PDF)
Drawing (PDF)	Application Specification AS-51300-005-001 (PDF)
Product Specification PS-51300-004-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	51300
Application	Panel-Mount, Wire-to-Wire
Component Type	Housing
Overview	CRC™ (Compact Robotic Connectors)
Product Name	CRC™
Type	N/A
UPC	800756548531


Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Stainless Steel
Material - Plating Mating	N/A
Material - Resin	Polyester
Net Weight	3099.700/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
Packaging Type	Tray
Panel Mount	Front, Rear
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Polarized to PCB	N/A
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No

Electrical

Current - Maximum per Contact	15.0A
Shielded	Yes
Voltage - Maximum	250V AC (RMS)/DC

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[51300](#) Series

Mates With

[55887](#) CRC™ Shielded Rectangular I/O Plug Assembly, [55891](#) Plug Housing

Use With

CRC™ Shielded Rectangular I/O Receptacle Shell [56377](#) , CRC™ Shielded Rectangular I/O Female Terminal [56194](#) Male Terminal

Reference - Drawing Numbers

Application Specification

Product Specification

Sales Drawing

AS-51300-005-001

PS-51300-004-001, PS-51300-005-001

SD-51300-003

This document was generated on 02/15/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51300-0411](#)