

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0512980471

Status:

Active

Overview:

CRC (Compact Robotic Connectors)

Description:

CRC Shielded Rectangular I/O Receptacle Assembly Set, Wire-to-Wire, Female Terminal, Power, 4 Circuits, Polarization Type A, Lead-Free



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	I/O Connectors
Series	51298
Application	Wire-to-Wire
Component Type	Housing
Overview	CRC (Compact Robotic Connectors)
Product Name	CRC
Type	N/A
UPC	800756691275

Physical	
Circuits (Loaded)	4
Circuits (maximum)	4
Durability (mating cycles max)	100
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	Polyester
Net Weight	44473.064/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	5.80mm
Polarized to Mating Part	Yes
Polarized to PCB	N/A
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No

Electrical	
Current - Maximum per Contact	15.0A
Shield Type	Upper Shielding
Shielded	Yes
Voltage - Maximum	250V AC (RMS)/DC

Material Info

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

51298 Series

Mates With

56193 CRC Power Crimp Pin, 55887 CRC Shielded Rectangular I/O Plug Assembly

Use With

CRC Shielded Rectangular I/O Female Terminal 56194

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51298-0471](#)