

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0526101433

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 14 Circuits, Tin-Silver-Bismuth Plating



Series image - Reference only

Documents:

- [3D Model \(PDF\)](#)
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-52610-032-001 \(PDF\)](#)
[Packaging Specification SPK-52610-003-001 \(PDF\)](#)
- [Datasheet \(PDF\)](#)
[Product Guide \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Reference Guide \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	FFC/FPC Connectors
Series	52610
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
UPC	887191316123

Physical

Actuator Type	Slider
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	30
Flammability	94V-0
Mated Height	5.75mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Silver-Bismuth
Material - Plating Termination	Tin-Silver-Bismuth
Material - Resin	Nylon
Net Weight	692.600/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.00mm
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Material Info

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52610 Series

Mates With

Premo-Flex FFC Cable [15167](#) , [98267](#) ,
[15267](#)

Reference - Drawing Numbers

Packaging Specification	SPK-52610-003-001
Product Specification	PS-52610-032-001
Sales Drawing	SD-52610-048-001, SD-52610-049-001

This document was generated on 07/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52610-1433](#)