

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0526102833

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 28 Circuits, Tin-Silver-Bismuth Plating

- Documents:
- 3D Model (PDF)

Datasheet (PDF)
- Drawing (PDF)

Product Guide (PDF)
- 3D Model

RoHS Certificate of Compliance (PDF)
- Product Specification PS-52610-032-001 (PDF)

Reference Guide (PDF)
- Packaging Specification SPK-52610-003-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

FFC/FPC Connectors

Series

52610

Overview

Easy-On FFC FPC Connectors

Product Name

Easy-On

Series Name

Slider

UPC

887191316284

Physical

Actuator Type

Slider

Circuits (Loaded)

28

Circuits (maximum)

28

Color - Resin

Natural

Contact Position

N/A

Durability (mating cycles max)

30

Flammability

94V-0

Mated Height

5.75mm

Material - Metal

Phosphor Bronze

Material - Plating Mating

Tin-Silver-Bismuth

Material - Plating Termination

Tin-Silver-Bismuth

Material - Resin

Nylon

Net Weight

1249.900/mg

Number of Rows

1

Orientation

Vertical

PC Tail Length

2.00mm

PCB Locator

No

PCB Mounting

Surface Mount

PCB Retention

None

Packaging Type

Embossed Tape on Reel

Pitch - Mating Interface

1.00mm

Pitch - Termination Interface

1.00mm

Polarized to PCB

No

Stackable

No

Temperature Range - Operating

-40° to +85°C

Wire/Cable Type

FFC/FPC

Electrical

Current - Maximum per Contact

1.0A

Voltage - Maximum

125V

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

52610 Series

Mates With

Premo-Flex FFC Cable [15167](#) , [98267](#) ,
[15267](#)

Reference - Drawing Numbers

Packaging Specification	SPK-52610-003-001
Product Specification	PS-52610-032-001
Sales Drawing	SD-52610-048-001, SD-52610-049-001

This document was generated on 07/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52610-2833](#)