

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0563773000

Status:

Active

Overview:

CRC (Compact Robotic Connectors)

Description:

CRC Shielded Rectangular I/O Receptacle Shell, Panel Mount, Signal, 30 Circuits, Front Mount Type



Series image - Reference only

Documents:	
3D Model	Product Specification PS-51238-010-001 (PDF)
Drawing (PDF)	Application Specification AS-51238-011-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	I/O Connectors
Series	56377
Application	Panel-Mount, Wire-to-Wire
Component Type	Panel Mount Shell
Overview	CRC (Compact Robotic Connectors)
Product Name	CRC
Type	N/A
UPC	800756205847

Physical	
Circuits (Loaded)	30
Circuits (maximum)	30
Durability (mating cycles max)	100
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Material - Plating Mating	Nickel
Material - Resin	Polyester
Net Weight	24947.560/mg
Orientation	Vertical
PCB Locator	No
Packaging Type	Tray
Panel Mount	Front
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Polarized to PCB	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No

Electrical	
Current - Maximum per Contact	3.0A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers	
Application Specification	AS-51238-011-001
Product Specification	PS-51238-010-001
Sales Drawing	SD-56377-006-001

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen	China RoHS
---	------------

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
56377 Series

Use With
CRC Shielded Rectangular I/O Receptacle
Housing 51233 , 51238

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[56377-3000](#)