

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0563775000

Status:

Active

Overview:

CRC (Compact Robotic Connectors)

Description:

CRC Shielded Rectangular I/O Receptacle Shell, Panel Mount, Signal, 50 Circuits, Front Mount Type



Series image - Reference only

Documents:	
3D Model	Product Specification PS-51238-017-001 (PDF)
3D Model (PDF)	Product Specification PS-51300-001-001 (PDF)
Drawing (PDF)	Application Specification AS-51238-017-001 (PDF)
Product Specification PS-51238-016-001 (PDF)	RoHS Certificate of Compliance (PDF)

General		EU ELV Not Relevant	
Product Family	I/O Connectors	EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen For more information, please visit Contact US	
Series	56377	China RoHS	
Application	Panel-Mount, Wire-to-Wire	China ROHS Green Image	
Component Type	Panel Mount Shell	ELV Not Relevant	
Overview	CRC (Compact Robotic Connectors)	RoHS Phthalates Not Contained	
Product Name	CRC		
Type	N/A		
UPC	756054154755		
Physical			
Circuits (Loaded)	50		
Circuits (maximum)	50		
Durability (mating cycles max)	100		
Gender	Receptacle		
Keying to Mating Part	Yes		
Lock to Mating Part	Yes		
Material - Metal	Zinc Alloy		
Material - Plating Mating	Nickel		
Material - Resin	Polyester		
Net Weight	31929.600/mg		
Orientation	Vertical		
PCB Locator	No		
Packaging Type	Tray		
Panel Mount	Front		
Pitch - Mating Interface	N/A		
Polarized to Mating Part	Yes		
Polarized to PCB	No		
Surface Mount Compatible (SMC)	N/A		
Temperature Range - Operating	-40° to +105°C		
Termination Interface: Style	N/A		
Waterproof / Dustproof	No		
Electrical			
Current - Maximum per Contact	2.5A		
Shield Type	Full Shield		
Shielded	Yes		
Voltage - Maximum	250V AC (RMS)/DC		
Material Info			
Reference - Drawing Numbers			
Application Specification	AS-51238-017-001		
Product Specification	PS-51238-016-001, PS-51238-017-001, PS-51300-001-001		
Sales Drawing	SD-56377-015-001		

Search Parts in this Series
56377 Series

Use With
CRC Shielded Rectangular I/O Receptacle
Housing 51233 , 51238

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[56377-5000](#)