

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0558363070](#)
Status: **Active**
Overview: CRC (Compact Robotic Connectors)
Description: CRC Shielded Rectangular I/O Plug Assembly Set, Male Terminal, Signal, 30 Circuits, Polarization Type Standard, Lead-Free

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family I/O Connectors
Series [55836](#)
Application Wire-to-Wire
Component Type Kit
Overview [CRC \(Compact Robotic Connectors\)](#)
Product Name CRC
Type N/A
UPC 822350372718

Physical

Circuits (Loaded) 30
Circuits (maximum) 30
Color - Resin Black, Gray
Durability (mating cycles max) 100
Gender Plug
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Metal Phosphor Bronze, Stainless Steel
Material - Plating Mating Gold
Material - Resin Polyester
Net Weight 44452.016/mg
Number of Rows 6
Orientation Vertical
PCB Locator No
Packaging Type Tray
Panel Mount No
Pitch - Mating Interface 3.00mm
Pitch - Termination Interface 3.00mm
Polarized to Mating Part Yes
Polarized to PCB No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Crimp or Compression
Waterproof / Dustproof No

Electrical

Current - Maximum per Contact 3.0A
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing SD-55836-006-001, SD-55836-006-002,
SD-55836-006-003, SD-55836-006-004,
SD-55836-006-005



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[55836](#) Series

Mates With

CRC Shielded Rectangular I/O Receptacle
[54333](#) , [54334](#)

This document was generated on 09/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

55836-3070