

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018839

Status:

Active

Overview:

Application Tooling


Description:

Impact Daughtercard Module Installation Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	887191064666
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	ATS-622018839-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

170340 Impact Daughtercard 85 Ohm Assembly 170340 Series, (4-Pair by 12 Column Assemblies)

Application Tooling Description	FAQ Product #
Impact 85 Ohm Plus 4 Pair, Right-Angle Daughtercard, Unguided, 12 Columns, 144 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1703401022
Impact 85 Ohm Plus 4 Pair, Right-Angle Daughtercard, Left Guided, 12 Columns, 144 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1703403022

Impact 85 Ohm Plus 1703405022
4 Pair, Right-Angle
Daughtercard, Right
Guided, 12 Columns,
144 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead Free
Impact 85 Ohm Plus 764951228
4 Pair RAM Signal
Module, Unguided,
Dual Endwalls,
12 Columns, 144
Circuits, Pin Length
5.50mm, Plated
Through Hole
Dimension 0.39mm,
Lead Free

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8839](#)