

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018959

Status:

Active

Overview:

Application Tooling

Description:

Impel Daughtercard Module Installation Press-In Tool


Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impel
Tool Type	Press-Fit Insertion Tool
UPC	887191324494
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	622018959-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ECHA_01_2020 (16 January 2020)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With

171320 Impel 1.9mm Pitch Daughtercard Module Assembly, 4-Pair by 8-Column Assemblies

Application Tooling Description	FAQ Product #
Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Unguided, 8 Columns, 64 Circuits, Plated Through Hole Dimension 0.36mm	1713201038
Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Left Guided, 8 Columns, 64 Circuits, Plated	1713203038

Through Hole
Dimension 0.36mm
Impel 90 Ohm, 4 1713205038
Pair Right-Angle
Daughtercard,
1.90mm Pitch,
Right Guided, 8
Columns, 64 Circuits,
Plated Through Hole
Dimension 0.36mm
Impel 90 Ohm 4 1721401808
Pair Right-Angle
Header, 1.90mm
Pitch, Unguided, 8
Columns, 64 Circuits,
Pin Length 5.50,
Plated Through Hole
Dimension 0.36
Impel 90 Ohm 4 Pair 1721403808
Right-Angle Header,
1.90mm Pitch, Right
Guided, 8 Columns,
64 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.36mm
Impel 90 Ohm, 4 1721405808
Pair Right-Angle
Header, 1.90mm
Pitch, Left Guided, 8
Columns, 64 Circuits,
Pin Length 5.50,
Plated Through Hole
Dimension 0.36mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8959](#)