

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0621009630

Status:

Active

Overview:

Application Tooling

Description:

Impel Backplane Press-In Tool


Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	887191179742
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-621009630-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per -ED/01/2018 (15 January 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With

171335 Impel Backplane Assembly, 3-Pair by 8 Column Assemblies

Application Tooling Description	FAQ Product #
IMPEL 3Px8C BP Assy Ungd Open 4.90 0.46	1713351804
Impel 90 Ohm, 3 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Open Endwalls, 8 Columns, 48 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm	1713351805
Impel 90 Ohm, 3 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided,	1713351807

Open Endwalls, 8
Columns, 48 Circuits,
Pin Length 4.90mm,
Plated Through Hole
Dimension 0.36mm
Impel 90 Ohm, 3 Pair 1713351808
Vertical Backplane
Header, 1.90mm
Pitch, Unguided,
Open Endwalls, 8
Columns, 48 Circuits,
Pin Length 5.50mm,
Plated Through Hole
Dimension 0.36mm

This document was generated on 06/26/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62100-9630](#)