

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622020500

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for RJ-45 CAT5, CAT5e, CAT6, CAT6A Plugs, 22-28 AWG



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Function	Insulation Displacement (IDT)
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	800756500027
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Physical	
Net Weight	597.000/g
Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	ATS-622020500-001, TM-638000029-001

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/30/2017 (7 July 2017) Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series	
207129 Series	
Use With	
44915 CAT 6 Modular Plugs	
Application Tooling FAQ	
Description	Product #
Modular Plug, Category 6, Long Body, Unshielded, 8/8	449150001
Modular Plug, Category 6, Long Body, Shielded, 8/8, without Strain Relief	449150011
Modular Plug, Category 6, Long Body, Shielded, 8/8, without Strain Relief	449150012
Modular Plug, Category 6, Long Body, Shielded, 8/8, with Strain Relief	449150021

Modular Plug, Category 6, Long Body, Shielded, 8/8, with Strain Relief	<u>449150022</u>
---	------------------

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62202-0500](#)