

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0638026200
Status: Active
Overview: Application Tooling
Description: Mini-Mac Applicator Rear Feed

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series 207127
Comments See Tooling Specification (PDF) Above
Function Crimp
Geographic Area Global
Level of Automation Automatic, Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview Application Tooling
Product Name Mini-Mac
Tool Type Applicator
UPC 883906944285
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 3328.939/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents ATS-638026200-001, TM-638000100SP-001



Series image - Reference only

EU ELV
Not Relevant
EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Relevant
For more information, please visit [Contact US](#)
China ROHS Not Relevant
ELV Not Relevant
RoHS Phthalates Not Reviewed

Search Parts in this Series
207127 Series

Use With
Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Flag InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Metal Strip, Tab 6.35 x 0.81mm	190070008
Flag InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Metal Strip, Tab 4.75 x 0.51mm	190070014
Flag InsulKrimp Quick Disconnect, Female, for 18-22	190070020

(0.80-0.35mm²) Wire,
Metal Strip, Tab 4.75
x 0.81mm
InsulKrimp Female 190070066
Fully Insulated Quick
Disconnect Flag for
18-22 AWG Wire,
Tab 6.35 x 0.81mm,
94 V-0 Material,
Metal Strip

This document was generated on 10/07/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63802-6200](#)