

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638118700

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for SL Crimp Terminals, 22-24 AWG and 32-26 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

Field Repair, See Tooling Specification (PDF) Above.

Type: 4D

Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

800756875354

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

332.600/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638118700-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
SL Crimp Terminal, Series 70058, Female, 32-36 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	16020074
SL Crimp Terminal, Series 70021, Male, with 0.38µm Selective Gold (Au) Plated Contact, 22-24 AWG, Reel	16020081
SL Crimp Terminal, Series 70058, Female, 32-36 AWG, with 0.76µm	16020085

Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, [16020086](#)
Series 70058,
Female, 22-24 AWG,
with Tin (Sn) Plated
Contact, Reel
SL Crimp Terminal, [16020087](#)
Series 70058,
Female, 22-24
AWG, with 0.38μm
Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, [16020088](#)
Series 70058,
Female, 22-24
AWG, with 0.76μm
Selective Gold (Au)
Plated Contact, Reel
SL Crimp Terminal, [16020101](#)
Series 70058,
Female, 32-36
AWG, with 0.76μm
Selective Gold (Au)
Plated Contact, Bag
SL Crimp Terminal, [16020102](#)
Series 70058,
Female, 22-24 AWG,
with Tin (Sn) Plated
Contact, Bag
SL Crimp Terminal, [16020103](#)
Series 70058,
Female, 22-24
AWG, with 0.38μm
Selective Gold (Au)
Plated Contact, Bag
SL Crimp Terminal, [16020104](#)
Series 70058,
Female, 22-24
AWG, with 0.76μm
Selective Gold (Au)
Plated Contact, Bag
SL Crimp Terminal, [16020107](#)
Series 70021, Male,
with Tin (Sn) Plated
Contact, 22-24 AWG,
Reel
SL Crimp Terminal, [16020114](#)
Series 70021, Male,
with Tin (Sn) Plated
Contact, 22-24 AWG,
Bag
SL Crimp Terminal, [16020115](#)
Series 70021,
Male, with 0.38μm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Bag
SL Crimp Terminal, [16020116](#)
Series 70021,
Male, with 0.76μm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Reel

SL Crimp Terminal, [16020117](#)
Series 70021,
Male, with 0.76µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Bag
SL Crimp Terminal, [16021110](#)
Series 71851,
Female, with Tin
(Sn) Plated Contact,
22-24 AWG, Reel
SL Crimp Terminal, [16021111](#)
Series 71851,
Female, with 0.76µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Reel
SL Crimp Terminal, [16021114](#)
Series 71851,
Female, with Tin
(Sn) Plated Contact,
22-24 AWG, Bag
SL Crimp Terminal, [16021115](#)
Series 71851,
Female, with 0.76µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Bag
SL Crimp Terminal, [16021124](#)
Series 71851,
Female, with 0.38µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Reel
SL Crimp Terminal, [16021125](#)
Series 71851,
Female, with 0.38µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Bag
SL Crimp Terminal, [700210081](#)
Series 70021,
Male, with 0.38µm
Selective Gold (Au)
Plated Contact,
22-24 AWG, Reel
SL Crimp Terminal, [700580102](#)
Female, 22-24 AWG,
with Tin (Sn) Plated
Contact, Unplated
Edges, Bag
SL Crimp Terminal, [700580103](#)
Female, 22-24
AWG, with 0.38µm
Selective Gold (Au)
Plated Contact, Bag
SL Crimp Terminal, [700580104](#)
Female, 22-24
AWG, with 0.76µm
Selective Gold (Au)
Plated Contact, Bag
SL Crimp Terminal, [700584086](#)
Series 70058,
Female, 22-24 AWG,
with Tin (Sn) Plated

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63811-8700](#)