

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638132400

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for 0.60mm CP Crimp Terminals for CMC Connector

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207121
Comments	See Tooling Specification Above. Extraction Tool for removal of 98913 Series
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800756720210
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638132400-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207121 Series

Use With

64322 , 98913 0.6mm (.02") CP Crimp Terminal for CMC connector

Application Tooling Description	FAQ Product #
0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.35mm²	643221019
0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.75mm²	643221029
0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.5mm²	643221039

0.635mm CMC CP	643221219
Female Terminal,	
Tin Plated, Selective	
1.27µm Gold in	
Contact Area, for	
Square 0.6mm x	
0.6mm Pins, Wire	
Size 0.75mm ²	
0.635mm CMC CP	643221229
Female Terminal,	
Tin Plated, Selective	
1.27µm Gold in	
Contact Area, for	
Square 0.6mm x	
0.6mm Pins, Wire	
Size 0.35mm ²	
0.635mm CMC CP	643221239
Female Terminal,	
Tin Plated, Selective	
1.27µm Gold in	
Contact Area, for	
Square 0.6mm x	
0.6mm Pins, Wire	
Size 0.5mm ²	
0.635mm CMC CP	643221339
Female Terminal,	
HP Version, Tin	
Plated, Selective	
1.27µm Gold in	
Contact Area, for	
Square 0.60mm x	
0.60mm Pins, Wire	
Size 0.75mm ²	
0.635mm CMC CP	643221349
Female Terminal,	
HP VERSION, Tin	
Plated, Selective	
1.27µm Gold in	
Contact Area, for	
Square 0.6mm x	
0.6mm Pins, Wire	
Size 0.35mm ²	
0.635mm CMC CP	643221359
Female Terminal,	
HP VERSION, Tin	
Plated, Selective	
1.27µm Gold in	
Contact Area, for	
Square 0.6mm x	
0.6mm Pins, Wire	
Size 0.5mm ²	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63813-2400](#)