

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638195400

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for 10, 12, 14 AWG Power Contact Terminals



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above. Type: 4C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	883906429775
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-6381954HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

42262 Crimp Terminal Power Contact

Application Tooling Description	FAQ Product #
---------------------------------	---------------

EXTreme	1736934632
Ten60Power Crimp Terminal, Female, Power Contact, Select Gold (Au) Stripe over Tin (Sn), 10-12 AWG	
9.14mm Pitch Crimp Terminal, Power Contact, Tin (Sn), All Over Nickel (Ni) with Select Gold, 10-12 AWG	442624332
9.14mm Pitch Crimp Terminal, Power Contact, Tin (Sn), All Over Nickel (Ni) with	442624432

Select Gold, 10-12
AWG
9.14mm Pitch Crimp [442624532](#)
Terminal, Power
Contact, Tin (Sn), All
Over Nickel (Ni) with
Select Gold, 10-12
AWG
9.14mm Pitch Crimp [442624632](#)
Terminal, Power
Contact, Tin (Sn), All
Over Nickel (Ni) with
Select Gold, 10-12
AWG
5.33mm Pitch Crimp [442626311](#)
Terminal, Power
Blade, Tin
5.33mm Pitch Crimp [442626312](#)
Terminal, Power
Blade, Tin
5.33mm Pitch Crimp [442626320](#)
Terminal, Power
Blade, Select Gold
Strips over Tin
5.33mm Pitch Crimp [442626321](#)
Terminal, Power
Blade, Select Gold
Strips over Tin
5.33mm Pitch Crimp [442626322](#)
Terminal, Power
Blade, Select Gold
Strips over Tin

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63819-5400](#)