

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639008200

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for Male and Female Terminals, 14-16 AWG Wire

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	883906513160
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	5020.127/g

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-639008200-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
MX150L Male Terminal for 14-16 AWG Wire, Metal Strip Carrier, Length 25.40mm	194170011
MX150L Male Terminal for 14-16 AWG Wire, Metal Strip Carrier, Length 25.40mm , Gold Plated	194170025
MX150L Male Terminal for 14-16 AWG Wire, Metal	194170027

	Strip Carrier, Length 26.16mm	
	MX150L Male	<u>194170029</u>
	Terminal for 14-16 AWG Wire, Length 26.16mm , Metal Strip Carrier, Gold Plated	
	MX150L Female	<u>194200001</u>
	Terminal for 14-16 AWG Wire, Tin Plated, Metal Strip Carrier	
	MX150L Female	<u>194200003</u>
	Terminal for 14-16 AWG Wire, Gold Plated, Metal Strip Carrier	

This document was generated on 10/07/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63900-8200](#)