

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0673298000

Status:

Active

Overview:

USB Products and Solutions

Description:

Universal Serial Bus (USB) Shielded I/O Receptacle, Type A, Single Upright Right-Angle, Solder Tail Length 2.00mm, Kinked Pins, PCB Thickness 1.20mm and 1.60mm, Gold (Au) Flash, Lead-Free

Documents:


3D Model

Packaging Specification PK-67329-001-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

3D Model (PDF)



Series image - Reference only

Agency Certification		
UL		E29179
General		
Product Family		I/O Connectors
Series		67329
Application		Wire-to-Board
Comments		Standard Mount Type
Component Type		Receptacle
Overview		USB Products and Solutions
Product Name		USB
Standard		USB 2.0
Type		A
UPC		822350416887

Physical		
Circuits (Loaded)		4
Circuits (maximum)		4
Color - Resin		Black
Flammability		94V-0
Gender		Female
Lock to Mating Part		Yes
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Mounting Style		Upright
Net Weight		2.025/g
Number of Rows		4
Orientation		Right Angle
PC Tail Length		2.00mm
PCB Locator		Yes
PCB Retention		Yes
PCB Thickness - Recommended		1.60mm
Packaging Type		Tray
Panel Mount		No
Pitch - Mating Interface		N/A
Pitch - Termination Interface		1.40mm
Plating min - Mating		0.102µm
Plating min - Termination		2.540µm
Polarized to Mating Part		Yes
Polarized to PCB		Yes
Ports		1
Surface Mount Compatible (SMC)		Yes
Termination Interface: Style		Through Hole
Waterproof / Dustproof		No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

67329 Series

Mates With

USB Type A Plug

Electrical

Current - Maximum per Contact	1.0A
Shield Type	Full Shield
Shielded	Yes

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-67329-001-001
Sales Drawing	SD-67329-801-001

This document was generated on 08/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[67329-8000](#)